

CUTTING



MOUNTING



POLISHING



HARDNESS TESTING



PRESSURE VESSEL



常温硬化樹脂の気泡抜きを手軽に行うことができる圧力器です。

北川グレステック株式会社

〒262-0013

千葉県千葉市花見川区犢橋町1614-27

Tel : 047-301-5408 Fax : 047-301-5709



A STRONG WORLDWIDE PRESENCE THROUGH SUBSIDIARIES AND MORE THAN 35 DISTRIBUTORS



FUNCTIONALITIES

REF. 43000



常温硬化樹脂の気泡を非常に簡単に取り除くことができる圧力器です。コンプレッサーから圧縮空気を吸入口に流し込むだけで使用することができます。特に真空脱泡機で気泡を抜くことができないほど短時間で硬化するアクリル樹脂KMシリーズを使用する際にこの容器を用いると収縮を低減し、気泡を大きく除去することができます。

ACCESSORIES

Accessories for cold mounting

- 04111**
Set of 100 holding blue clips (plastic)
- 04900**
Set of 100 polypropylene plastic cups
- 04024**
Box of 5 graduated measuring cups (250 cc) with stirring sticks
- 04112**
Set of 100 holding (multi-colour) clips

Rubber silicone mounting moulds

- 04021**
Silicone Rubber Ø 25mm
- 04022**
Silicone Rubber Ø 30mm
- 04023**
Silicone Rubber Ø 40mm
- 04025**
Rectangular 55 x 30 x 25mm
- 04026**
Rectangular 70 x 40 x 25mm
- 04027**
Rectangular 100 x 50 x 25mm

Polyethylene mounting moulds

- 04028**
Polyethylene Ø 25mm
- 04029**
Polyethylene Ø 30mm
- 04030**
Polyethylene Ø 40mm

Teflon (PTFE) mounting moulds

- 04016**
Teflon (PTFE) Ø 20mm
- 04017**
Teflon (PTFE) Ø 25mm
- 04036**
Teflon (PTFE) Ø 25.4mm
- 04018**
Teflon (PTFE) Ø 30mm
- 04037**
Teflon (PTFE) Ø 31.7mm
- 04038**
Teflon (PTFE) Ø 38.1mm
- 04019**
Teflon (PTFE) Ø 40mm
- 04020**
Teflon (PTFE) Ø 50mm

KM mounting moulds

- 04048**
Kit 50 KM rings + 5 bases Ø 25mm
- 04049**
Kit 50 KM rings + 5 bases Ø 30mm
- 04050**
Kit 50 KM rings + 5 bases Ø 40mm

KM moulds reloads

- 04045**
50 rings* Ø 25mm
- 04046**
50 rings* Ø 30mm
- 04047**
50 rings* Ø 40mm

* For use with KM mould bases

Additional accessories

- 53605**
50 protection sheets
- 53606**
Pipes and plastic nozzles (set of 50)



REF. 04111



REF. 04900



REF. 04024



REF. 04112



REF. 04022



REF. 04029



REF. 04018



MOULE KM

PRESI IS ALSO...

CUTTING



Mecatome ST 310

MOUNTING



Mecapress 3

POLISHING



Mecattech 334

HARDNESS TESTING



Microtech MX1

CONSUMABLES



Resins



FIND OUT MORE AT
WWW.PRESI.COM

